

CONFIGURATIONS

Notes

- In order to make capacitor banks, it is necessary to use suitable discharge resistors and current peak limiting systems upon insertion, compatibly with the characteristics of the capacitors (25 A / μ F).

Table

THD(I)max. = 10% on the network

Code	Capacitance μ F	50 Hz			Terminals	Execution	Dimensions D x H
		kVAr	V	A			
8302475	3 x 31	5	415	7	faston 6,3	resin	70 x 200
8302481	3 x 47	7,5	415	10,4	faston 6,3	resin	70 x 200
8302579	3 x 62	10	415	14	M8	resin	85 x 200
8302588	3 x 77	12,5	415	17,4	M8	resin	85 x 200
8302599	3 x 92	15	415	20,9	M8	resin	85 x 295
8302600	3 x 123	20	415	27,8	M8	resin	85 x 295
8302622	3 x 154	25	415	34,8	morsetto	resin	100 x 285
8304811	3 x 55	10	440	13,1	M8	resin	85 x 200
8304813	3 x 66	12,5	440	16,4	M8	resin	85 x 200
8304804	3 x 109	20	440	26,2	morsetto	resin	100 x 350
83048085	3 x 137	25	440	32,8	morsetto	resin	100 x 350
8304838	3 x 164	30	440	39,4	morsetto	resin	120 x 350
8304852	3 x 219	40	440	52,5	morsetto	resin	136 x 350
8304854	3 x 274	50	440	65,6	morsetto	resin	136 x 350
8306790	3 x 69	15	480	18	M8	resin	85 x 295
8306799	3 x 115	25	480	30	morsetto	resin	120 x 225
83068075	3 x 154	33,4	480	40,2	morsetto	resin	136 x 230
83068115	3 x 38	10	525	11	M8	resin	85 x 200
8307031	3 x 48	12,5	525	13,7	M8	resin	85 x 200
8307032	3 x 57,8	15	525	16,5	M8	resin	85 x 295
8306819	3 x 77	20	525	22	morsetto	resin	100 x 350
8306827	3 x 96	25	525	27,5	morsetto	resin	120 x 350
8306832	3 x 115	30	525	33	morsetto	resin	120 x 350
8306840	3 x 154	40	525	44	morsetto	resin	136 x 350
8306910	3 x 67	10	690	8,4	morsetto	resin	100 x 285
8306900	3 x 83	12,5	690	10,5	morsetto	resin	100 x 285
8306920	3 x 133	20	690	16,7	morsetto	resin	100 x 285
8306925	3 x 167	25	690	20,9	morsetto	resin	120 x 350

Other solutions are available upon request.